

AC-11 Actuator

Large Handle • Flush Mount





- Rear mount installation
- Flush mounting style
- Single, multi-point or direct pull actuation
- Multiple key code options
- Non-locking option



Material and Finish

Housing, handle, linkage: glass-filled nylon, black

Threaded stud and cable bracket retainers: steel, zinc nickel plated

Housing and handle gaskets: Adhesive backed foam, black

Installation Notes

Mounting nut (M6 x 1) not supplied. Installation torque of mounting nuts not to exceed 7 Nom (62 in-lbf)

Notes

AC-11 can only use snub end coupling (Type 6 or 7 cable).

Part Number Selection Notes:

For use with Rods / Cables, recommended Snap-in Retainer for Rotator Plate: Southco Part Number R4-0-43922. See Trade Drawing J-R4-0-43922 for more details and options.

For lock core selection, detailed key information and a complete overview of the SOUTHCO® Key-Choice System see PK Lock Cores section.

For unique key code options, please contact customer service.

Other ontions available. For complete details on variety, part numbers, installation and specification, go to



www.southco.com/AC

S Actuation Style 🔫

- Single Point, Direct Pull
- Multi-Point, without Cable Bracket 2
- Multi-Point, with Cable Bracket

AC - 11 - S L 1 - 11 - KC

L Locking Options

- Non-Locking
- Reversible key (No keys R001)
- Reversible key (2 keys included R001) 2
- 3 Reversible key (keyed differently - 2 keys included)
- Standard key (No keys CH751)
- Standard key (2 keys included CH751) 5
- 6 Standard key (keyed differently - 2 keys included)
- Reversible Key (2 keys included 14603)
- No Lock Plug installed (See notes for more information)

KC Kev Codes ◀

(Omit for Locking Options 0, 1, 2, 4, 5 and 9)

- *KD10 Keyed Differently (Only used if L = 3 or 6)
- *MK10 Master Keyed Differently (Only used if L =6)

*Supplied in multiples of 10 with 10 different key codes.



Dimensions in millimeters (inch) unless otherwise stated